

OIL-FREE HEEL GUIDE PLATES

OIL-FREE HEEL GUIDE PLATES

Without bolt hole (W=50-70)

With bolt holes (W=50-70)

(W=100-120-150-180)

OGG

OGP

OGPZ (Counterbore machining type)

Material: S45C Special solid lubricant (embedded) 55HRC ~ (Induction hardening)

Without bolt hole (W=50-70)

With bolt holes (W=50-70)

(W=100-130-150)

GWZ

GWAZ

GWBZ

Material: S45C Special solid lubricant (embedded) 55HRC ~ (Induction hardening)

This product was discontinued in 2017.

Catalog No. : GWZ GWAZ GWBZ

W	T	S	OGP-OGPZ						Catalog No. Type	W	L	Base unit price 1~9 pieces		
			ℓ ₁	ℓ ₂	w ₁	d ₁	d ₂	t				OGG	OGP	OGPZ
50	30	60	20	50	18	26	18	OGG	50	160	Quotation			
		120	50	200										
		120	80	260										
70	35	100	60	70	26	18	OGG	70	230	Quotation				
		160	60						260					
		160	75						300					
100	45	100	60	90	32	22	OGG	100	230	Quotation				
		160	60						280					
		160	100						330					
120	45	100	60	120	32	22	OGP	120	230	Quotation				
		160	60						280					
		160	100						330					
150	50	100	60	150	32	22	OGPZ	150	280	Quotation				
		190	80						330					
		190	140						390					
180	55	160	60	180	32	22	OGPZ	180	280	Quotation				
		190	80						330					
		190	140						390					

Order **Catalog No. — L**
OGP 50 — 160

Days to Ship **Quotation**

Price **Quotation**

- Lubricate the plates before use. (initial greasing)
- The special solid lubricant embedded in the grooves continuously provides a lubricant film according to the load.
- The plate can slide only in the direction to L dimension.

T	GWAZ-GWBZ						Number of grooves	S	Catalog No. Type	W	L	Base unit price 1~9 pieces		
	ℓ ₁	ℓ ₂	C	d	D	t						GWZ	GWAZ	GWBZ
30	20	50	—	18	26	18	3	60	GWZ	50	160	Quotation		
							5	90			190			
							7	120			220			
35	25	60	—	18	26	18	6	100	GWZ	70	230	Quotation		
							9	140			270			
							11	180			310			
45	30	90	60	22	32	22	8	130	GWAZ	100	350	Quotation		
							11	180			400			
							14	230			400			
50	30	120	80	22	32	22	9	150	GWBZ	130	350	Quotation		
							12	200			400			
							16	250			450			
60	35	150	100	22	32	22	11	180	GWBZ	150	420	Quotation		
							14	230			470			
							18	280			520			

Order **Catalog No. — L**
GWBZ 50 — 160

Price **Quotation**

Days to Ship **Quotation**