


OUTSIDE RINGS FOR L ADJUSTABLE TYPE




Guide P.569

RoHS



② Outside Ring



Outside Ring

D	LA	ℓ_1	ℓ_2	ℓ_3	M (Coarse thread)	g	d
6	12	8	4	1.0	M3	1.0	5.5
8	14	10	5	1.0	M4	1.0	7.5
10	16	12	6	1.5	M5	1.5	9.5

SUS420
50~53HRC

Outside rings on this page are adapted for combination with inside arrows of date marked pin sets on P.573 and products on P.590.



① Inside Arrows P.573



Inside arrows is common with PL exchange type

③ Date Mark Adjusting Pins P.590



Non JIS material definition is listed on P.1351 - 1352

② Outside Ring Month · Day Type

Indication	Outside rings divisions	Part Number		U/Price 1~9
		Type	D	
Month	12 uniform divisions	DTDXL-R	6	Quotation
			8	
			10	
Day (1st digit)	10 uniform divisions	DTEXL-R	6	Quotation
			8	
			10	
Day (2nd digit)	12 uniform divisions	DTFXL-R	6	Quotation
			8	
			10	

Order Part Number
DTDXL-R10

Days to Ship Quotation

Price Quotation

Character Designation Type

Indication							
1M (1 place)	2M (2 places)	3M (3 places)	4M (4 places)	5M (5 places)	6M (6 places)	10M (10 places)	12M (12 places)
Engraving position 	Engraving position 	Engraving position 	Engraving position 	Engraving position 	Engraving position 	Engraving position 	Engraving position
Up to 3 characters can be designated at each engraving position.				Up to 2 characters can be designated at each engraving position.		Only 1 character can be designated at each engraving position.	

Part Number		Engraving characters (1~3 characters · Characters printed in blue in indications)						U/Price 1~9											
Type	Indication	Engraving position ①~⑫																	
DTXL-R	1M																		
	2M																		
	3M																		
	4M																		
	5M																		
	6M																		
10M																			
12M																			

Use ¥ for indicating / (slash), # for - (minus), and % for [] (space).

Dividing of outside rings

1M · 2M · 3M · 4M · 6M · 12M	12 uniform divisions
5M · 10M	10 uniform divisions

Order Part Number

① Characters for engraving	② Characters for engraving	③ Characters for engraving	④ Characters for engraving	⑤ Characters for engraving	⑥ Characters for engraving	⑫ Characters for engraving
DTXL-R 3M 6 -	POM	PS	SAN			
DTXL-R 6M10 -	09	10	11	12	13	14
DTXL-R12M10 -	%	1	2	3	4	5 ... F

Days to Ship Quotation

Price Quotation

Date Marked Pins
Recycle Marked Pins
Pins with Gas Vent