

MATERIAL GUIDE ROLLER SETS

—BEARING TYPE—

MATERIAL GUIDE ROLLER SETS

—OIL-FREE BUSHING TYPE—

RoHS

Single guide **GDRTA** (Roller bearing type)
GDRTB (Ball bearing type)

Double guides **GDRTAW** (Roller bearing type)
GDRTBW (Ball bearing type)

① **M** SCM415
F 55HRC~
② **M** SS400
A Hexagon socket head set screw (Cone point)
Single guide 1 piece
Double guides 2 pcs.

RoHS

Guide roller unit **GDRTAT** (Roller bearing type)
GDRTBT (Ball bearing type)

Details of A

A Hexagon socket head set screw (Cone point) 1 piece


Set parts

T	H	ℓ	d	A	B	C	P	R	E	F	(G)	D ₁	Catalog No.		Base unit price 1~9 sets	
													Type	D	W	Single guide
48	40	5	10	95 (395)	30	10	73 (373)	5.5	20	1.5	(300)	14	30	38	12,936	26,544
54	75	8	25	145 (445)	55	20	115 (415)	6.5	35	5.5		32	55	70	16,800	34,524
86	75	8	25	145 (445)	55	20	115 (415)	6.5	35	5.5		32	55	70	19,152	39,312
48	40	5	9	95 (395)	30	10	73 (373)	5.5	20	1.5		12	30	38	11,760	24,108
54	75	8	20	145 (445)	55	20	115 (415)	6.5	35	5.5	(300)	32	55	38	15,540	31,920
86	75	8	20	145 (445)	55	20	115 (415)	6.5	35	5.5		32	55	70	17,640	36,204

Numbers in () are the dimensions of the double guides (GDRTAW and GDRTBW).

Individual parts

T	H	ℓ	d	F	D ₁	L	t	d ₁	S	N	Catalog No.		Base unit price 1~9 pieces	
											Type	D		W
48	40	5	10	1.5	14	67	5.5	8	2.5	7	(Roller bearing type)	30	38	10,349
54	75	8	25	5.5	32	92	9.5	22	5	17	GDRAT	55	38	13,440
86	75	8	25	5.5	32	124	9.5	22	5	17	GDRAT	55	70	15,322
48	40	5	9	1.5	12	67	5.5	7	2.5	7	(Ball bearing type)	30	38	9,408
54	75	8	20	5.5	32	92	9.5	17	5	17	GDRBT	55	38	12,432
86	75	8	20	5.5	32	124	9.5	17	5	17	GDRBT	55	70	14,112



Order Catalog No. — W
GDRTA 55 — 38

Dispatch **7** Days

Price **Volume discount price** P.37

Quantity	1~9	10~19	20~29	30~50
Discount rate	Base unit price	5%	10%	15%

For larger orders, ask about prices/delivery.

RoHS

Single guide **EGDR**

Double guides **EGDRW**

① Roller
M SCM415
F 55HRC~
② CSR (Spool retainer)
③ Hexagon socket head cap screw
④ Oil-free bushing (LF type)
⑤ Snap ring (C type)
⑥ Spacer
⑦ Spring washer
⑧ Mounting plate
M SS400

RoHS

Guide roller unit **EGDR**

① Roller
M SCM415
F 55HRC~
② CSR (Spool retainer)
③ Hexagon socket head cap screw
④ Oil-free bushing (LF type)
⑤ Snap ring (C type)
⑥ Spacer
A Spring washer
D30---CBW10 1 piece
D55---CBW16 1 piece

Set parts

T	H	ℓ	d	d ₁	A	B	C	P	R	E	F	(G)	D ₁	Catalog No.		Base unit price 1~9 sets		
														Type	D	W	Single guide	Double guides
48	40	5	16	18	95 (395)	30	10	73 (373)	5.5	20	19		24	EGDR	30	38	6,888	14,700
54	75	8	25	28	145 (445)	55	20	115 (415)	6.5	35	30.5	(300)	36	EGDRW	55	70	9,324	18,984
86	75	8	25	28	145 (445)	55	20	115 (415)	6.5	35	30.5		36	EGDRW	55	70	10,500	21,252

Numbers in () are the dimensions of the double guides (EGDRW).

Individual parts

T	H	L	ℓ	d	F	S	D ₁	d ₁	M	Catalog No.		W	Base unit price 1~9 pieces
										Type	D		
48	40	52	5	16	19	15	24	18	10	EGDRT	30	38	4,704
54	75	61	8	25	30.5	26	36	28	16	EGDRT	55	38	6,048
86	75	93	8	25	30.5	24	36	28	16	EGDRT	55	70	6,972

Order Catalog No. — W
EGDR 55 — 38

Dispatch **7** Days

Price **Volume discount price** P.37

Quantity	1~9	10~19	20~29	30~50
Discount rate	Base unit price	5%	10%	15%

For larger orders, ask about prices/delivery.

RoHS

GDRA

① **M** SKS93
F 55~60HRC
② **M** SS400

Order Catalog No.
GDRA 30

Dispatch **7** Days

Price **Volume discount price** P.37

Quantity	1~9	10~19	20~29	30~50
Discount rate	Base unit price	5%	10%	15%

For larger orders, ask about prices/delivery.