


Arched Pull Handles / Cast Pull Handles




Arched Pull Handles

UWSD



RoHS 10



Part Number	L	L1	H	h	H1	Allowable Load (N)	Mass (g)	Unit Price
Type	L	L1	H	h	H1	Allowable Load (N)	Mass (g)	Unit Price
UWSD	100	139	42	27	22	500	337	
	150	190	44	29	20		434	

Ordering Example
Part Number
UWSD150

Example




Cast Pull Handles

UWASND



RoHS 10




Part Number	L	L1	H	h	T	A	W	R	N Through/Countersink	Allowable Load (N)	Mass (g)	Unit Price
Type	L	L1	H	h	T	A	W	R	N Through/Countersink	Allowable Load (N)	Mass (g)	Unit Price
UWASND	80	96	32	20	6	18	12	20	4.5 8.5	500	97	
	100	116						23			116	
	150	170	46	30	9	22	16	30	6.5 12.5		301	
	200	220	46	30	9	22	16	30	6.5 12.5		354	

Cast Pull Handles

UWANDC




RoHS 10



Part Number	L	L1	H	h	t	R	d	N	Allowable Load (N)	Mass (g)	Unit Price
Type	L	L1	H	h	t	R	d	N	Allowable Load (N)	Mass (g)	Unit Price
UWANDC	105	120	30	24	5	25	7.5	5.5	500	83	
	115	130	33	27	5	26	7.5	5.5		90	
	125	145	34	28	5.5	30	10	6.5		106	

Ordering Example
Part Number
UWASND100
UWANDC125

Folding Pull Handles / Pull Handles with Caps / Aluminum Tube Pull Handles




Folding Pull Handles

Type	Material	Surface Treatment
UWFASN	S45C	Chrome Plating
UWFASNS	SUS304	Buffing




RoHS 10



Part Number	L	L1	Allowable Load (N)	Mass (g)	Unit Price
Type	L	L1	Allowable Load (N)	Mass (g)	Unit Price
UWFASN (Steel)	138	100	650	150	
	158	120	550	160	
UWFASNS (Stainless Steel)	180	142	520	180	
	218	180	500	200	

Ordering Example
Part Number
UWFASN138

Pull Handles with Caps




RoHS 10

Part Number	L	Mass (g)	Applicable Screw	Unit Price
Type	L	Mass (g)	Applicable Screw	Unit Price
HHDG	100	62	Flat Head Screw M5	2
HHGGS				

Ordering Example
Part Number
HHDG100

Nut for Pull Handles with Caps




RoHS 10

Part Number	P	Applicable Handle	Unit Price	Volume Discount Rate
Type	P	Applicable Handle	Unit Price	Volume Discount Rate
HHPUW	100	HHDG100 HHGGS100		1 ~ 9 pc (s). 10 ~ 100

Ordering Example
Part Number
HHPUW100

Aluminum Tube Pull Handles




RoHS 10

Part Name
Tube Handle
Elbow

Part Number	L	Applicable Screw	Unit Price
Type	L	Applicable Screw	Unit Price
UWAPN (L Fixed)	150	Flat Head Screw M8	
	200		
	250		
	300		
	400		
	500		
	600		

Ordering Example
Part Number
UWAPN 150
UWAPFC 185
* is not necessary for L Fixed Type.

Small Diameter Aluminum Tube Pull Handles



RoHS 10

Part Name
Tube Handle
Elbow

Part Number	L	Applicable Screw	Unit Price
Type	L	Applicable Screw	Unit Price
UWAPNC (L Fixed)	100	Hex Socket Head Cap Screw M6	
	150		
	200		
	250		
	300		

Part Number	L	Applicable Screw	Unit Price
Type	L	Applicable Screw	Unit Price
UWAPFC (L Configurable)	100-150	Hex Socket Head Cap Screw M6	
	151-200		
	201-250		
	251-300		