





DIN Type
SKD61 equivalent
+
Nitrided

STEPPED EJECTOR PINS

—STANDARD TYPE—



D-ENSFB



- 📍 Range of guaranteed shaft diameter precision (D) and hardness (Details **P.61, 63**)
- 📍 Step R (Details **P.62**)
- 📍 SKD61 equivalent + Nitrided
- 📍 Surface 900HV ~ Material 40 ~ 45HRC

H	T	Part No.		L Selection	P	N
		Type	D			
3	1.5	D-ENSFB	1.5	100	0.8	40
				160	1.0	50
4	2		2	100	1.0 1.5	40
				160	50	
			200	75		
5	2		2.5	100	1.5	40
				160	1.5 2.0	50
6	3		3	100	1.0 1.5	40 75
				125	1.0 1.5 2.0	50 75
				160		
				200	1.5 2.0 2.5	75

📍 Nitriding may extend to the head as it is applied after dimension P machining.



Order

Part No. — L — P — N
D-ENSFB 3 — 100 — P1.0 — N40



Days to Ship



Stock



Price

Order / Quote:
WOS: <https://in.misumi-ec.com/>
TEL: +91-124-468-8800 E-mail: cs@misumi.co.in

