





DIN Type
SUJ2 equivalent
Hardened

STRAIGHT EJECTOR PINS

—STANDARD TYPE—



10PACK—D—EPU
D—EPU



① Range of guaranteed shaft diameter precision and hardness (Details **P.61, 63**)
 M SUJ2 equivalent
 H 58~62HRC

H	T	P g6	Part No.		L Selection									
			Type	P	100	125	160	200	250	315	400	500		
2.5	1.2	-0.002 -0.008	10PACK—D—EPU (for 10 pcs) D—EPU (for 1 pc)	1	100	125	160	200	250					
				1.1	100	125	160							
				1.2	100	125	160							
3	1.5	-0.002 -0.008		1.5	100	125	160	200	250	315	400			
2				100	125	160	200	250	315					
4	2	-0.004 -0.012		2	100	125	160	200	250	315	400			
5				100	125	160	200	250	315					
6				100	125	160	200	250	315	400	500			
7	3	-0.004 -0.012		3.5	100	125	160	200	250	315				
4				100	125	160	200	250	315	400	500			
8				100	125	160	200	250	315					
4.5				100	125	160	200	250	315					
10	3	-0.004 -0.012		5	100	125	160	200	250	315	400	500		
				5.5	100	125	160	200						
12	5	-0.005 -0.014		6	100	125	160	200	250	315	400	500		
				6.5	100	125	160	200	250	315	400			
14	5	-0.005 -0.014		7	100	125	160	200	250	315	400			
8				100	125	160	200	250	315	400	500			
9				100	125	160	200	250	315	400				
16	5	-0.005 -0.014		10	100	125	160	200	250	315	400	500		
18			100	125	160	200	250	315	400	500				
12			100	125	160	200	250	315	400	500				
22	7	-0.006 -0.017	14	125	160	200	250	315	400					
			16	100	125	160	200	250	315	400	500			
24	7	-0.006 -0.017	18	125	160	200	250	315	400	500				
20			100	125	160	200	250	315	400	500				
26	8	-0.007	20	100	125	160	200	250	315	400	500			



Order

Part No. — L
10PACK—D—EPU 3 — 100



Days to Ship

Stock



Price

Order / Quote:

WOS: <https://in.misumi-ec.com/>

TEL: +91-124-468-8800 E-mail: cs@misumi.co.in

