


JIS Type
SKD61 equivalent
+
Nitrided

STRAIGHT EJECTOR SLEEVES



—◎0.05 DIMENSIONS SPECIFY TYPE—



Part No.		D · P Tolerance	V Tolerance	Applicable center pin shaft diameter tolerance
Diameter select	Diameter specify			
C-ESNV-L	C-ESNVB	-0.01 -0.02	H7	-0.01 -0.02

*Please note that the ejector sleeve with a V dimension tolerance of H7 has a long precision fitting portion S and is not suitable for use with a center pin with a shaft diameter tolerance of ± 0.005 .

VH7 Tolerance		
$V \leq 3.0$	$3.1 \leq V \leq 6.0$	$V \geq 6.1$
+0.010 0	+0.012 0	+0.015 0



Dimension C remains unchanged

Range of guaranteed shaft diameter precision ($b_1 = L - x_1$)
x1 max.40

- SKD61 equivalent + Nitrided
- Surface: 900HV~
- Material: 40±3HRC

⚠ Nitriding may extend to the head as it is applied after dimension V and D (or P) machining.

⚠ When the diameter (D) portion of the stepped center pin is inserted into the relief hole (C), make sure relief hole (C) \geq pin diameter (D) + 1.0

Ejector Sleeves

■ Diameter (D) select type

H	Part No.		L	V	C	Cmax.	S
	Type	D					
7	C-ESNV-L	4	40.00~200.00	1.5~2.5	C \geq V + 0.5	3.0	20~50
		4.5					
8	C-ESNV-L	5	40.00~250.00	2.0~3.0	C \geq V + 0.5	3.5	20~50 (⚠ D4, D4.5 When (V1.5~V1.9) 20~40)
		5.5					
9	C-ESNV-L	6	40.00~300.00	2.0~4.0	C \geq V + 0.5	4.0	20~50 (⚠ D4, D4.5 When (V1.5~V1.9) 20~40)
		6.5					
10	C-ESNV-L	7	40.00~300.00	2.0~5.0	C \geq V + 0.5	4.5	20~50 (⚠ D4, D4.5 When (V1.5~V1.9) 20~40)
		7.5					
11	C-ESNV-L	8	40.00~300.00	2.0~5.5	C \geq V + 0.5	5.0	20~50 (⚠ D4, D4.5 When (V1.5~V1.9) 20~40)
		8					
14	C-ESNV-L	9	40.00~300.00	2.5~6.0	C \geq V + 0.5	5.5	20~50 (⚠ D4, D4.5 When (V1.5~V1.9) 20~40)
		9					
15	C-ESNV-L	10	40.00~300.00	2.5~8.0	C \geq V + 0.5	6.0	20~50 (⚠ D4, D4.5 When (V1.5~V1.9) 20~40)
		10					

■ Diameter (P) 0.01 mm specify type

H	Part No.		L	P	V	C	Cmax.	S
	Type	No.						
7	C-ESNVB	4	40.00~200.00	3.50~3.99	1.5~1.9	C \geq V + 0.5	2.4	20~50
		5						
8	C-ESNVB	5	40.00~250.00	4.01~4.99	2.0~2.9	C \geq V + 0.5	3.4	20~50 (⚠ No.4, No.4.5 When (V1.5~V1.9) 20~40)
		5.5						
9	C-ESNVB	6	40.00~250.00	5.01~5.49	2.0~3.4	C \geq V + 0.5	3.9	20~50 (⚠ No.4, No.4.5 When (V1.5~V1.9) 20~40)
		6						
10	C-ESNVB	6.5	40.00~300.00	5.51~5.99	2.0~3.9	C \geq V + 0.5	4.4	20~50 (⚠ No.4, No.4.5 When (V1.5~V1.9) 20~40)
		7						
11	C-ESNVB	7	40.00~300.00	6.01~6.49	2.0~4.4	C \geq V + 0.5	4.9	20~50 (⚠ No.4, No.4.5 When (V1.5~V1.9) 20~40)
		7.5						
15	C-ESNVB	8	40.00~300.00	7.01~7.49	2.0~5.4	C \leq P - 1.5	5.4	20~50 (⚠ No.4, No.4.5 When (V1.5~V1.9) 20~40)
		8						
15	C-ESNVB	10	40.00~300.00	7.51~7.99	2.5~5.9	C \leq P - 1.5	5.9	20~50 (⚠ No.4, No.4.5 When (V1.5~V1.9) 20~40)
		10						

⚠ V \leq P - 2.0



Order

Part No. — L — P — V — C — S
 (Diameter D select type) C-ESNV-L 8 — 200.05 — V4.1 — C5.0 — S32
 (Diameter P specify type) C-ESNVB 8 — 200.05 — P7.55 — V4.1 — C5.0 — S32



Days to Ship

12 Days



Price

Order / Quote:

WOS: <https://in.misumi-ec.com/>
 TEL:+91-124-468-8800 E-mail:cs@misumi.co.in



Alterations

Part No. — L — P — V — C — S — (KC · WKC...etc.)
 C-ESNV-L 8 — 200.05 — V4.1 — C4.6 — S32 — KC4.5
 C-ESNVB 8 — 150.00 — P7.55 — V4.0 — C5.0 — S32 — KC3.75

Alteration details P.68