



JIS Type
SKD61 equivalent
+
Nitrided

STRAIGHT EJECTOR PINS

—STANDARD TYPE—



① Range of guaranteed shaft diameter precision and hardness
(Details see P.61, 63)

Part No.	Head thickness	T Tolerance
C-EPN	4mm (T4)	$0_{-0.02} (L > 300 \cdots 0_{-0.05})$
C-EPJ	6*8mm (JIS)	$0_{-0.05}$

P Tolerance

L	P	1~13	15~20
L ≤ 500		$-0.01_{-0.02}$	$-0.01_{-0.03}$
L ≥ 600		$-0.01_{-0.03}$	$-0.01_{-0.03}$

M SKD61 equivalent+Nitrided
H Surface: 900HV~
Material: 40~45HRC

Head thickness 4mm		Head thickness JIS		Part No.		L Selection
H	T	H	T	Type	P	
				Head thickness 4mm	Head thickness JIS	
3				C-EPN	1	100 150
4					1.5	100 150 200
5					2	100 150 200 250 300 *350*400
6					2.5	100 150 200 250 300 350 400
7					3	100 150 200 250 300 350 400 *450 *500
8					3.5	100 150 200 250 300 350 400 450 500
8	8				4	100 150 200 250 300 350 400 (500)
9	9	6			4.5	100 150 200 250 300 350 400 (500)
10	10				5	100 150 200 250 300 350 400 500 (600)
11	11				*5.5	100 150 200 250 300 350 400 500
15	15			C-EPJ	6	100 150 200 250 300 350 400 500 (600) (700)
17	17	8			*6.5	100 150 200 250 300 350 400 500 (600) (700)
21	21				7	100 150 200 250 300 350 400 500 *600 *700 *800 *900 *(1000)
25	25				8	100 150 200 250 300 350 400 (450) 500 (600) (700) (800) *900 *(1000)
					10	100 150 200 250 300 350 400 (450) 500 (600) (700) (800) *900 *(1000)
					12	100 150 200 250 300 350 400 (450) 500 (600) (700) (800) *900 *(1000)
					16	100 150 200 250 300 350 400 500 600 700 800 *900 *1000
					20	150 200 250 300 400 500 600 700 *800 *900 *1000

① The L dimension enclosed in brackets () is applicable only for C-EPJ. ② Nitriding may extend to the head as it is applied after dimension P machining.



Order

Part No. — L
C-EPN 3 — 100



Days to Ship

without *

Stock

with *

10 Days



Price

Order / Quote:

WOS: <https://in.misumi-ec.com/>

TEL: +91-124-468-8800 E-mail: cs@misumi.co.in



Alterations



Part No. — L — (KC · WKC...etc.)
C-EPN 16 — 500 — KC8



10 Days

Alteration details see P.28

Alterations	Code	Spec.	
	KC	Single flat cutting $P/2 \leq KC < H/2$	About Designation Unit for Key Flat Cutting (1) To align the key flat with the shaft diameter Unit of designation 0.05mm increments possible
	WKC	Two parallel flats cutting $P/2 \leq WKC < H/2$	(2) To designate arbitrary key flat dimensions Unit of designation 0.1mm

Alterations	Code	Spec.
	HC	HC=0.1mm increments ① $P+1 \leq HC < H$ and $P \geq 1.5$
	TC	TC=0.1mm increments ① $T/2 \leq TC < T$ and $P \geq 1.5$ ② Dimension L becomes shorter by (T-TC)

