


JIS Type  
SKD61 equivalent  
+  
Nitrided

# STRAIGHT EJECTOR SLEEVES

— ◎ 0.08 L DIMENSION SPECIFY TYPE —



Part No.	V Tolerance	Applicable center pin shaft diameter tolerance	D Tolerance		V <sub>H7</sub> Tolerance			
			D ≤ 12	D ≥ 15	V ≤ 3	3.5 ≤ V ≤ 6	6.5 ≤ V ≤ 10	V ≥ 12
C-ESJL	H7	-0.01 -0.02	-0.01 -0.02	-0.01 -0.03	+0.010 0	+0.012 0	+0.015 0	+0.018 0



⚠ Nitriding may extend to the head as it is applied after dimension V and D machining.

⚠ The value of S is set in accordance with the specified L dimension. S=L-Z

L	80.00~100.00	100.01~120.00	120.01~140.00	140.01~160.00	160.01~180.00	180.01~225.00	225.01~250.00	250.01~275.00	275.01~300.00	300.01~325.00	325.01~350.00	350.01~375.00	375.01~400.00	400.01~425.00	425.01~450.00	450.01~475.00	475.01~500.00
L-S	50 (60)	70 (80)	90 (100)	85	105	125	150	175	185	210	235	225	250	275	300	325	350

⚠ The value in ( ) is only applicable to V1.5.

⚠ The diameter (D) portion of the stepped center pin cannot be inserted into the relief hole (C) of C-ESJL type.

Range of guaranteed shaft diameter precision (b1=L-x1) SKD61 equivalent+Nitrided Surface: 900HV~ Material: 40±3HRC

H	T	Part No.		L 0.01mm increments	V Selection
		Type	D		
8	6	C-ESJL	4	80.00~140.00	1.5 2 2.5
				140.01~200.00	2 2.5
4.5			80.00~140.00	1.5 2 2.5	
			140.01~200.00	2 2.5	
9			5	80.00~225.00	2 2.5 3
				225.01~300.00	3
5.5			80.00~225.00	2 2.5 3	
			225.01~300.00	3	
10			6	80.00~300.00	2 2.5 3 3.5 4
				300.01~450.00	3 3.5
6.5			80.00~300.00	2 2.5 3 3.5 4	
			300.01~450.00	3 3.5 4	
11	7	80.00~300.00	2 2.5 3 3.5 4 4.5		
		300.01~450.00	3 3.5 4 4.5		
7.5	80.00~300.00	3 3.5 4 4.5			
	300.01~375.00	3.5 4 4.5			
13	8	80.00~300.00	2 2.5 3 3.5 4 4.5 5 5.5		
		300.01~450.00	3 3.5 4 4.5 5		
450.01~500.00	5				
	80.00~300.00	2 2.5 3 3.5 4 4.5 5 5.5			
300.01~450.00		3 3.5 4 4.5 5			
	450.01~500.00	5 5.5 6			
15		10	80.00~450.00	4 4.5 5 5.5 6 6.5 7	
	450.01~500.00		5 5.5 6 6.5 7		
17	12	80.00~450.00	4 4.5 5 5.5 6 6.5 7 8 8.5		
		450.01~500.00	5 5.5 6 6.5 7 8		
20	15	180.01~500.00	9 10		
		25	180.01~500.00	12 15	



Order

Part No. — L — V  
C-ESJL 6.5 — 115.50 — V2.5



Days to Ship

10 Days



Price

Order / Quote:  
WOS: <https://in.misumi-ec.com/>  
TEL: +91-124-468-8800 E-mail: cs@misumi.co.in



Alterations

Part No. — L — V — (KC · WKC...etc.) Alteration details P.68  
C-ESJL 8 — 200.05 — V4 — KC4.0