





JIS Type  
SKD61 equivalent  
Hardened

# STRAIGHT EJECTOR PINS

— L DIMENSION SPECIFY TYPE —

Total length specified type



☉ Range of guaranteed shaft diameter precision and hardness  
(Details see P.61, 63)

☒ SKD61 equivalent  
☒ 50~55HRC

Part No.	Head thickness	T P Tolerance
C-EPD-L	4mm (T4)	-0.01 -0.02

H	T	Part No.		L 0.01mm increments
		Type	P	
3	4	C-EPD-L (P <sup>-0.01</sup> <sub>-0.02</sub> )	1.5	40.00~200.00
4			2	40.00~250.00
5			2.5	40.00~300.00
6			3	
7			3.5	
8			4	40.00~500.00
9			4.5	
10			5	
11			5.5	
14			6	
15			6.5	
17			7	
18			8	
			9	
			10	
			12	
			13	



Order

Part No. — L  
C-EPD-L 2.5 — 80.00



Days to Ship

10 Days



Price

Order / Quote:  
WOS: <https://in.misumi-ec.com/>  
TEL:+91-124-468-8800 E-mail:cs@misumi.co.in



Alterations

Part No. — L — (KC · WKC...etc.)  
C-EPD-L 3 — 80.00 — TC2.0

Alteration details see P.28

Alterations	Code	Spec.	
	KC	Single flat cutting $P/2 \leq KC < H/2$	About Designation Unit for Key Flat Cutting (1) To align the key flat with the shaft diameter (Unit of designation) 0.05mm increments possible
	WKC	Two parallel flats cutting $P/2 \leq WKC < H/2$	(2) To designate arbitrary key flat dimensions (Unit of designation) 0.1mm

Alterations	Code	Spec.	
	HC	HC=0.1mm increments ☉ $P+1 \leq HC < H$	
	HCC	HCC=0.1mm increments ☉ $P+1 \leq HCC < H-0.3$	
	TC	TC=0.1mm increments ☉ $2.0 \leq TC < 4$ (Dimension L remains unchanged.) ☉ $4-TC \leq L_{max} - L$	