


JIS Type
SKD61 equivalent
+
Nitrided

EJECTOR BLADES

— DIMENSIONS SPECIFY TYPE —



H	T	Part No.		L	P	W	K max.	N	
		Type	D						
6	4	C-ERNX	2	100.00~200.00	0.80~1.80	0.30~	1.9	· D2~9 $N \geq 30$ and $(L-N) \geq 30$ · D10~16 $N \geq 50$ · D20~25 $N \geq 55$ and $N \geq \frac{L}{3}$ $(L-N) \geq 10$	
			2.5	100.00~250.00	0.80~2.30	0.30~	2.4		
			3		0.80~2.80	0.30~	2.9		
7	6		3.5	100.00~300.00	1.00~3.30	0.30~	3.4		
8			4		1.00~3.80	0.30~	3.9		
9			4.5		1.20~4.30	0.40~	4.4		
10	8		5	100.00~500.00	1.50~4.80	0.40~	4.9		
11			5.5		1.80~5.30	0.50~	5.4		
13			6		2.00~5.80	0.50~	5.9		
14	8		6.5	200.00~500.00	2.00~6.30	0.50~	6.4		
15			7		2.50~6.80	0.50~	6.9		
17			8		2.50~7.80	0.50~	7.9		
18	8		9	200.00~600.00	2.50~8.80	0.50~	8.9		
20			10		200.00~500.00	5.00~9.80	1.00~		9.9
21			12		6.00~11.80	1.00~	11.9		
25	8		13	200.00~700.00	6.00~12.80	1.00~	12.9		
20			15		8.00~14.80	1.50~	14.9		
21			16		8.00~15.80	1.50~	15.9		
30	8		20	200.00~700.00	10.00~19.70	2.00~	19.9		
30			25		13.00~24.70	2.50~	24.9		

Order **Part No.** - **L** - **P** - **W** - **N**
C-ERNX 15 - 505.00 - P10.00 - W5.00 - N170

Days to Ship **12** Days

Price **Order / Quote:**
WOS: <https://in.misumi-ec.com/>
TEL: +91-124-468-8800 E-mail: cs@misumi.co.in

Alterations **Part No.** - **L** - **P** - **W** - **N** - (AKC · AWC · etc.)
C-ERNX 15 - 505.00 - P10.00 - W5.00 - N170 - AKC 0

Alterations details P.28

Alterations	Code	Spec.
	AKC	AKC=1° increments ① 0 ≤ AKC < 360
	AWC	AWC=1° increments ① 0 ≤ AWC < 360
	ARC	ARC=1° increments ① 0 ≤ ARC < 360

Alterations	Code	Spec.
	ADC	ADC=1° increments ① 0 ≤ ADC < 360
	HC	HC=0.1mm increments ① D+1 ≤ HC < H
	TC	TC=0.1mm increments ① T/2 ≤ TC < T and T-TC ≤ Lmax. -L ② L, N Dimension L and N remain unchanged.