


RETURN PINS

—LENGTH SPECIFY TYPE—



Type	Head thickness (T)	Squareness of the head
C-RP4TL	4mm	
C-RP8TL	8mm	



⚠ A center hole may remain on one or both ends.

20Cr
 56HRC--
 (Depth 0.8 mm or more)

H	Df6		Part No.		L 0.1mm increments
			Type	D	
11	8	-0.013	C-RP4TL	8	35.0~250.0
15	10	-0.022		10	35.0~300.0
17	12	-0.016		12	35.0~300.0
18	13			13	35.0~300.0
20	15	-0.027		15	35.0~350.0
21	16	-0.020		16	35.0~350.0
25	20			20	50.0~400.0
30	25			25	50.0~450.0
35	30			30	50.0~450.0
15	10	-0.013 -0.022		C-RP8TL	10
17	12	-0.016	12		35.0~300.0
18	13		13		35.0~300.0
20	15	-0.027	15		35.0~350.0
21	16	-0.020	16		35.0~350.0
25	20		20		50.0~500.0
30	25		25		50.0~500.0
35	30		30		50.0~500.0
40	35	-0.025	35		100.0~500.0
45	40		40		100.0~500.0
55	50	-0.041	50	100.0~500.0	



Order

Part No. — L
C-RP4TL 20 — 199.0



Alterations



Part No. — L — (SC)
C-RP4TL 20 — 199.0 — SC



Days to Ship

12 Days



Price

Order / Quote:
WOS: <https://in.misumi-ec.com/>
TEL:+91-124-468-8800 E-mail:cs@misumi.co.in

Alteration	Code	Spec.																										
	SC	Adds two parallel flats on the head as shown in the figure (Spanner groove width alteration)																										
		<table border="1"> <thead> <tr> <th>D</th> <th>8</th> <th>10</th> <th>12</th> <th>13</th> <th>15</th> <th>16</th> <th>20</th> <th>25</th> <th>30</th> <th>35</th> <th>40</th> <th>50</th> </tr> </thead> <tbody> <tr> <td>B</td> <td>8</td> <td>10</td> <td>13</td> <td>13</td> <td>17</td> <td>17</td> <td>22</td> <td>27</td> <td>32</td> <td>35</td> <td>40</td> <td>50</td> </tr> </tbody> </table>	D	8	10	12	13	15	16	20	25	30	35	40	50	B	8	10	13	13	17	17	22	27	32	35	40	50
D	8	10	12	13	15	16	20	25	30	35	40	50																
B	8	10	13	13	17	17	22	27	32	35	40	50																