


# ANGULAR PINS

— TAPPED TYPE —



**C-APU** (Tapped type)



M 20Cr  
H 56HRC~  
 (Depth of more than 0.8 mm)

⦿ A center hole may remain on one or both ends. 
 ⦿ When  $D \geq 25$ , the spherical end complies with that in the above figure.

D	Press-fit section Dh7	Sliding part Df6	M	l	S	l1	W	Part No.		0.1mm increments	
								Type	D	L	N
13	0 -0.018	-0.016 -0.027	8	20	6.5	10	10	<b>C-APU</b>	13	$0 \leq N < L$	
16	0 -0.021	-0.020 -0.033	10	25	8	13	16		110.1~160.0		
									160.1~200.0		
20	0 -0.025	-0.025 -0.041	12	30	10	12	20		200.1~250.0		
									250.1~300.0		
25	0 -0.025	-0.025 -0.041	16	40	10	18	25		300.1~350.0		
									350.1~400.0		
30	0 -0.025	-0.025 -0.041	16	40	10	18	30		400.1~450.0		
									450.1~500.0		
35	0 -0.025	-0.025 -0.041	16	40	10	18	35	500.1~550.0			
								550.1~600.0			



Order

Part No. — L — N  
**C-APU 25 — 200.0 — N40.0**



Example

**Using AI (Screw Bolt)**

• Can also be set from the parting line using a hexagonal wrench.



C-APU



Days to Ship

**12** Days



Price

**Order / Quote:**  
 WOS: <https://in.misumi-ec.com/>  
 TEL:+91-124-468-8800 E-mail:cs@misumi.co.in