





DIN Type
SKD61 equivalent
Hardened

STEPPED EJECTOR PINS

— DIMENSIONS SPECIFY TYPE —



D—EDSF



- Range of guaranteed shaft diameter precision (D) and hardness (Details P.61, 63)
- Step R (Details P.62)
- SKD61 equivalent
- 50~55HRC

Ejector Pins

H	T	Part No.		L	P	N
		Type	D.	0.01mm increments	0.01mm increments	1mm increments
3	1.5	D—EDSF	1.5	40.00 ~ 200.00	0.80 ~ 1.40	N ≥ 15 and 15 ≤ (L - N) ≤ 150
4	2		2	40.00 ~ 315.00	0.80 ~ 1.90	
5			2.5		0.80 ~ 2.40	
6			3	40.00 ~ 400.00	1.00 ~ 2.90	
7			3.5	40.00 ~ 400.00	1.50 ~ 3.40	
8	3		4	50.00 ~ 500.00	1.50 ~ 3.90	
10			4.5	50.00 ~ 250.00	2.50 ~ 4.40	N ≥ L/3 and (L - N) ≥ 10
12	5		5	50.00 ~ 400.00	3.00 ~ 4.90	
14			5.5	50.00 ~ 200.00	3.50 ~ 5.40	
16			6	50.00 ~ 1000.00	4.00 ~ 5.90	
18	7		6.5	50.00 ~ 250.00	4.50 ~ 6.40	
22			8		5.90 ~ 7.90	
26	8		10		7.90 ~ 9.90	
			12	50.00 ~ 1000.00	8.90 ~ 11.90	
			16		11.90 ~ 15.90	
			20		15.90 ~ 19.90	



Alterations



Part No. — L — P — N — (KC · WKC...etc.)
D—EDSF 2 — 149.78 — P1.5 — N70 — KC1

Alteration details P.28

Alterations	Code	Spec.
	KC	Single flat cutting D/2 ≤ KC < H/2 (1) To align the key flat with the shaft diameter (Unit of designation) 0.05mm increments possible
	WKC	Two flats cutting D/2 ≤ WKC < H/2 (2) To designate arbitrary key flat dimensions (Unit of designation) 0.1mm

Alterations	Code	Spec.
	HC	HC = 0.1mm increments D + 1 ≤ HC < H



Order

Part No. — L — P — N
D—EDSF 2.5 — 149.78 — P1.5 — N70



Days to Ship

•D < 16 •D ≥ 16
10 Days 15 Days



Price

Order / Quote:

WOS: <https://in.misumi-ec.com/>

TEL: +91-124-468-8800 E-mail: cs@misumi.co.in

