




LIFTER UNITS

— FLAT SURFACE TYPE —



HAMMR



■ Components list

No.	Name	Qty.	Material & remarks
①	Lifting plate	1	Equivalent to SS400
②	Mounting base plate	1	Equivalent to SS400
③	Guide bushing	2	FC250 oil-free
④	Guide bar	2	S45C HRC50~60
⑤	Cylinder	1	Made by AIRTAC (for D=40) Made by AIRTAC (for D=63)

No.	Name	Qty.	Material & remarks
⑥	Link block	1	S45C
⑦	Hexagon socket head cap bolt	4	M 6 × 35 (For D=40) M 8 × 35 (For D=63)
⑧	Hexagon socket head cap bolt	4	M12 × 35
⑨	Nut	2	M35

H1	H2	Rc	W	W1	W2	W3	W4	L	L1	Catalog No.	Cylinder dia. D	Stroke ST
88	52	1/4	270	240	215	190	120	75	45	HAMMR	40	50
												75
												100
												125
												150
												175
												200
												225
												250
												275
98	75	3/8	290	260	235	215	145	90	70	HAMMR	63	50
												75
												100
												125
												150
												175
												200
												225
												250
												275
300												



Order

Catalog No. **HAMMR** D **40** - ST **100**



Alterations

Catalog No. **HAMMR** (D) **40** - ST **100** - (S) **S**



Days to Ship

Quotation




Price

Quotation



Example

See the illustration for the space for casting installation.



D	L	A	B
40	75	85	50
63	90	95	60

- Actual cylinder output
Air pressure: 500kPa
φ 40: approx. 600×0.7=420N
φ 63: approx. 1500×0.7=1050N